


SERIES 29

FEATURES


- Quick Connect/Disconnect
- Only 7/8" Above Board Height
- Standard, Insulated, or Banana Plug Styles
- High Temperature Spring Style
- Color Coded Caps with Optional Additional Colors



DESCRIPTION

Press button and put lead in slot and release. Spring pressure assures firm, positive contact.

DIMENSIONS In Inches (and millimeters)



SPECIFICATIONS

Rating Criteria

Rating: At 120 Vdc, 20 Amps continuously, with a maximum temperature rise of 20°C.

Materials and Finishes

External Metal Parts: Nickel plated brass

Spring: Tinned music wire Button Caps: Polyethylene

Washers (29-104): Black thermoset plastic High Temperature Spring: Stainless steel

OPTIONS

Green or White Caps Gold plate finish: Available on all but Banana Plug styles.

ORDERING INFORMATION

Description	Part Number	
Standard, without cap	29-110	
Standard, with red cap	29-100 RED	
Standard, with black cap	29-100 BLK	
High temperature standard, without cap	29-125	
Insulated, with black cap	29-104 BLK	
Insulated, with red cap	29-104 RED	
Banana plug, with black cap	29-101 BLK	
Banana plug, with red cap	29-101 RED	

Available from your local Grayhiil Distributor For prices and discounts, contact a local Sales Office, an authorized local Distributor, or Grayhill.