

## M12-P-ACC-HOUSING M FRONT MOUNTING



Image is for illustration purposes only. Please refer to product description.

|                    |                                                                                             |
|--------------------|---------------------------------------------------------------------------------------------|
| Part number        | 21 03 302 1001 407                                                                          |
| Specification      | M12-P-ACC-HOUSING M FRONT MOUNTING                                                          |
| HARTING eCatalogue | <a href="https://b2b.harting.com/21033021001407">https://b2b.harting.com/21033021001407</a> |

### Identification

|                              |                         |
|------------------------------|-------------------------|
| Category                     | Accessories             |
| Series                       | Circular connectors M12 |
| Type of accessory            | Housing                 |
| Description of the accessory | for front mounting      |

### Version

|              |                           |
|--------------|---------------------------|
| Gender       | Male                      |
| Locking type | Screw locking<br>PushPull |

### Technical characteristics

|                                        |                             |
|----------------------------------------|-----------------------------|
| Tightening torque                      | 2 Nm Lock nut               |
| Degree of protection acc. to IEC 60529 | IP65 / IP67 mated condition |

### Material properties

|                             |                                                        |
|-----------------------------|--------------------------------------------------------|
| Material (seal)             | NBR                                                    |
| Colour (seal)               | Grey                                                   |
| RoHS                        | compliant with exemption                               |
| RoHS exemptions             | 6(c): Copper alloy containing up to 4 % lead by weight |
| ELV status                  | compliant with exemption                               |
| China RoHS                  | 50                                                     |
| REACH Annex XVII substances | Not contained                                          |
| REACH ANNEX XIV substances  | Not contained                                          |



**Pushing Performance**  
Since 1945

## Material properties

|                                      |                      |
|--------------------------------------|----------------------|
| REACH SVHC substances                | Yes                  |
| REACH SVHC substances                | Lead                 |
| California Proposition 65 substances | Yes                  |
| California Proposition 65 substances | Lead                 |
| Fire protection on railway vehicles  | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels   | R26                  |

## Specifications and approvals

|                |                                                            |
|----------------|------------------------------------------------------------|
| Specifications | IEC 61076-2-010                                            |
| UL / CSA       | UL 1977 ECBT2.E102079<br>CSA-C22.2 No. 182.3 ECBT8.E102079 |
| PROFINET       | Yes                                                        |

## Commercial data

|                                |                                            |
|--------------------------------|--------------------------------------------|
| Packaging size                 | 30                                         |
| Net weight                     | 12 g                                       |
| Country of origin              | Romania                                    |
| European customs tariff number | 85389099                                   |
| GTIN                           | 5713140236387                              |
| ETIM                           | EC002943                                   |
| eCl@ss                         | 27440292 Connector component (accessories) |