

## M23 P Hood angl. 7-12mm rotatable



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 600 0603
Specification	M23 P Hood angl. 7-12mm rotatable
HARTING eCatalogue	<a href="https://b2b.harting.com/09156000603">https://b2b.harting.com/09156000603</a>

### Identification

Category	Hoods/Housings
Series	Circular connectors M23
Identification	Power
Type of hood/housing	Hood
Description of hood/housing	EMC version Rotatable

### Version

Size	M23
Version	Angled entry
Locking type	Screw locking

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Degree of protection acc. to IEC 60529	IP67 locked condition IP69 / IPX9K acc. to ISO 20653 locked condition
Clamping range	7 ... 12 mm

### Material properties

Material (hood/housing)	Copper-zinc alloy
Surface (hood/housing)	Nickel plated
RoHS	compliant
ELV status	compliant
China RoHS	e



**Pushing Performance**  
Since 1945

## Material properties

REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Not contained
California Proposition 65 substances	Yes
California Proposition 65 substances	Lead Nickel
Fire protection on railway vehicles	EN 45545-2 (2020-08)
Requirement set with Hazard Levels	R26

## Specifications and approvals

UL / CSA	UL 1977 ECBT2.E235076
----------	-----------------------

## Commercial data

Packaging size	5
Net weight	166.75 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140184268
ETIM	EC003556
eCl@ss	27440224 Shell for circular connectors