







SECTION A-A





SECTION A-A



G-Switch USB-C Specification:

- 1.Current rated: 5A on vbus/1.25A on vconn/0.25A on other
- 2.Withstanding voltage: 100V AC/minute
- 3.Contact resistance: 40mΩ Max
- 4.Insulation resistance: 100MΩ Min
- 5.Operating temperature: -40°C ~ +85°C
- 6.Mating force : 5N~20N
- 7.Unmating force: 8N~20N
- 8.Durability cycle:10,000 cycles



A1	A2	A3	A4	A5	A6	A7	A8	A9	A10	A11	A12
GND	TX1+	TX1-	VBUS	CC1	D+	D-	SBU1	VBUS	RX2-	RX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First
B12	B11	B10	B9	B8	B7	B6	B5	B4	B3	B2	B1
GND	RX1+	RX1-	VBUS	SBU2	D-	D+	CC2	VBUS	TX2-	TX2+	GND
First	Second	Second	First	Second	Second	Second	Second	First	Second	Second	First

1	SHELL	STAINLESS STEEL	Ni PLATED
2	MID PLATE	STAINLESS STEEL	Ni PLATED
3	HOUSING	HIGH TEMPERATURE PLASTIC	BLACK UL 94 V-0
4	TERMINALS	COPPER ALLOY	Au PLATING ON CONTACT AREA
5	EMI	STAINLESS STEEL	--
NO.	PARTS	MATERIAL	REMARKS

RECOMMENDED P.C.B. LAYOUT
TOLERANCE UNSPECIFIED ±0.05mm



SCALE: 1:1	UNIT: mm	Title: Horizontal Type-c 24P Female			
SIZE: A4		SMT CH=1.68 L=7.9mm Pin0.5mm			
Unless otherwise General Tolerance:		Molde Code: GT-USB-7013A03			
X.	±0.25	DRAWN	CHECKED	APPROVED	DATE
X.x	±0.20				
X.xx	±0.15				
X.xxx	±0.10				
X°	±5°	Xia	Chen	Chen	2023.02.01



REV: A0	SHEET: 1/1
---------	------------