



HOOD INTERNAL VIEW



OPTION 1*



OPTION 2*

* Hood can be of either Option 1 or Option 2

2	8630-CH25UNCLF	UNC 440
1	8630-CH25M3LF	M3
SL.NO.	PART NO:	THREAD



FCIconnect.com




Copyright FCI

"This LF product meets European Union Directives and other country regulations as described in GS-47-0004"

Packaging as per GS-14-920

MATERIAL:-

1. NYLON 6 30% GF UL 94V-0 (OPTIONAL)
2. ABS UNFILLED UL 94 HB (STANDARD)
3. TEMP RANGE -55°C +85°C

mat'l. code				surface <input checked="" type="checkbox"/> ISO 1302		tolerance <input checked="" type="checkbox"/> ISO 406 <input checked="" type="checkbox"/> ISO 1101		projection 		product family D-SUB				
ltr	ecn no	dr	date	tolerances unless otherwise specified		angles linear		MM 		title CONNECTOR HOOD 25 POSITION				
E	106-0074	MINI	2006/06/08											
F	110-0122	AMR	2010/05/29			.00±0.1								
G	110-0231	AMR	2010/11/27	0±1°				scale 2:1						
H	ELX-I-15622	MP	2013/08/24	dr	MINI K VANDANATH	1995/24/03			dwg no sheet 1 of 1 size					
J	ELX-I-21747	MP	2015/08/22	engr	MITHUN PAUL	2015/08/22			C-DSUB-0024 A3					
				chr	ALIAS BABU	2015/08/22								
				app	BIJU K PAUL	2015/08/22								
sheet index		revision sheet		J 1						type Product Customer Drawing				