





リール引き出し方向
DIRECTION OFF TOP OF REEL



B-B



DETAIL C
4:1




— DETAIL C

A—A

OBSOLETE

250	623243-1	1903277-1	1903291-1
QTY	EMBOSS P/N	CONNECTOR P/N	P/N

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位： 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		T.FUTATSUGI APVD 24NOV05 Y.YAMAMOTO		NAME 名称 EMBOSS ASSY 0.635mm PITCH BAY CONNECTOR PLUG WITH BOSS											
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		PRODUCT SPEC 製品規格 108-78235		SIZE A3				CAGE CODE 00779		DRAWING NO 番号 C-1903291		RESTRICTED TO			
MATERIAL 材料 		FINISH 仕上		WEIGHT		CUSTOMER DRAWING						SCALE 尺度 2:1		SHEET 1 OF 4		REV D1	


REVISIONS					
変更					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-

注記

1. 材料：
エンボステープ：PS
カバーテープ：PET
2. コネクタ寸法及び推奨基板取り付け寸法は、コネクタ単体の図面を参照下さい。
3. 一般公差：±0.3 、±3°








NOTE

1. MATERIAL :
EMBOSS TAPE : PS
COVER TAPE : PET
2. DIMENSION OF CONNECTOR AND RECOMMENDED P.C.BOARD LAYOUT : SEE CONNECTOR DRAWING.
3. GENERAL TOLERANCE: ±0.3 , ±3°




THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	TE Connectivity Ltd.		
		CHK			
DIMENSIONS: 単位： 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	APVD	NAME 名称 EMBOSS ASSY 0.635mm PITCH BAY CONNECTOR PLUG WITH BOSS		
	0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	PRODUCT SPEC 製品規格	SIZE CAGE CODE DRAWING NO 番号 A300779C-1903291		
	MATERIAL 材料	APPLICATION SPEC 取付適用規格	RESTRICTED TO		
		WEIGHT			
CUSTOMER DRAWING			SCALE 尺度 NTS	SHEET 2 OF 4	REV D1


SEE SHEET 1



1903277-1 : AS SHOWN
(REFERENCE)


THIS DRAWING IS A CONTROLLED DOCUMENT.		 TE Connectivity Ltd.	
DIMENSIONS: 单位: 耗 mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差	
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±	
MATERIAL 材料		FINISH 仕上	
			
CUSTOMER DRAWING		DWN CHK APVD PRODUCT SPEC 製品規格 APPLICATION SPEC 取付適用規格 WEIGHT	
NAME 名称		EMBOSS ASSY 0.635mm PITCH BAY CONNECTOR PLUG WITH BOSS	
SIZE	CAGE CODE	DRAWING NO 番号	RESTRICTED
A3	00779	C-1903291	
SCALE 尺度		SHEET	REV
4:1		3 OF 4	D1

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	-	SEE SHEET 1	-	-	-



RECOMMENDED P.C.BOARD LAYOUT
(REFERENCE)

- △ 材質：
ハウジング；熱可塑性樹脂(UL94V-0, 黒色)
コンタクト；銅合金
仕上げ；全面 ニッケル下地めっき
接点部 金めっき
半田付け部 すずめっき
ソルダーベグ；銅合金
仕上げ；全面すずめっき
- △ シーケンシャルピン(LONGピン)：左サイド6ピン(A19,20,21 B19,20,21)
右サイド6ピン(A1,2,3 B1,2,3)
両サイド計12ピン
- △ コネクタを平坦面に置き、タイン、ペグの浮きは0.1以下。



- △ MATERIAL
HOUSING：THERMO-PLASTICS(UL94V-0, BLACK)
CONTACT：COPPER ALLOY
FINISH：ALL OVER Ni UNDER PLATING.
Au PLATING ON CONTACT AREA.
TIN PLATING ON TINE AREA.
PEG：COPPER ALLOY
FINISH：ALL OVER TIN PLATING.
- △ SEQUENTIAL CONTACTS.(LONG CONTACTS)：
LEFT SIDE 6 PINS (A19,20,21 B19,20,21)
RIGHT SIDE 6 PINS (A1,2,3 B1,2,3)
BOTH SIDE TOTAL 12PINS
- △ MUST BE MEASURED FLOATING AMOUNT OF TINES & PEG
FROM DATUM SURFACE IS 0.1 MAX.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	 TE Connectivity Ltd.		
		CHK			
DIMENSIONS: 単位： 耗 mm		APVD	NAME 名称 EMBOSS ASSY 0.635mm PITCH BAY CONNECTOR PLUG WITH BOSS		
TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差		PRODUCT SPEC 製品規格			
MATERIAL 材料		APPLICATION SPEC 取付適用規格	SIZE	CAGE CODE	DRAWING NO 番号
		WEIGHT	A3	00779	C-1903291
		CUSTOMER DRAWING		SCALE 尺度	SHEET 4 of 4
				REV D1	