



[Home](#) > [Products](#) > [By Type](#) > [Relays](#) > [Product Feature Selector](#) > Product Details

## KC-38 Product Details



**KC-38**  
(7-1618278-6)

TE Internal Number: 7-1618278-6

**Active**

### High Voltage Relays

[Not EU RoHS or ELV Compliant](#)

#### Product Highlights:

- Contact Arrangement = 1 Form B, SPST-NC, 1 N/C
- Power Switching = No
- Contact Current Rating = 0 - 15 Amps.
- Not RF Rated
- Coil Voltage = 26.5 VDC

[View all Features](#)

### Quick Links

- [Check Pricing & Availability](#)
- [Search for Tooling](#)
- [Product Feature Selector](#)
- [Contact Us About This Product](#)

[Add to My Part List](#)

[Request Sample](#)

[Find Similar Products](#)

[Buy Product](#)

### Documentation & Additional Information

#### Product Drawings:

- None Available

#### Catalog Pages/Data Sheets:

- None Available

#### Product Specifications:

- None Available

#### Application Specifications:

- None Available

#### Instruction Sheets:

- None Available

#### CAD Files:

- None Available

#### Additional Information:

- [Product Line Information](#)

#### Related Products:

- [Tooling](#)

### Product Features (Please use the Product Drawing for all design activity)

#### Product Type Features:

- [Termination Style](#) = Turret Terminal

#### Electrical Characteristics:

- [Contact Current Rating \(Amps.\)](#) = 0 - 15
- [RF Rated](#) = No
- [Coil Voltage \(VDC\)](#) = 26.5
- [Voltage, Max. \(VDC\)](#) = 0 - 25000
- Current, Carry Only = Yes

#### Termination Related Features:

- [High Voltage Connection \(Power\)](#) = Bifurcated Terminals
- [High Voltage Connection \(Coil\)](#) = Turret Terminals
- [Auxiliary Contacts](#) = Without

#### Body Related Features:

- [Mount Style](#) = Threaded

#### Configuration Related Features:

- [Contact Arrangement](#) = 1 Form B, SPST-NC, 1 N/C
- [Power Switching](#) = No
- [Economizer](#) = Without

#### Industry Standards:

- [RoHS/ELV Compliance](#) = Not ELV/RoHS compliant
- [Lead Free Solder Processes](#) = Not suitable for lead free processing

#### Other:

- Brand = Kilovac

### Corporate Information

[Who We Are](#)  
[Investors](#)  
[News Room](#)  
[Supplier Portal](#)  
[Careers](#)

### Quick Links

[Check Distributor Inventory](#)  
[Cross Reference](#)  
[Find Documents & Drawings](#)  
[Product Compliance Support Center](#)  
[Site Map](#)

### Customer Support

[Email or Chat with Us](#)  
[Find a Phone Number](#)  
[Search Knowledge Base](#)  
[Manage Your Account](#)