


Specifications:
 Current rating:1 Amps
 Dielectric Withstanding:AC 500V
 Operating Temperature:-25°C ~ +105°C
 Contact resistance:20mohm max.
 Insulation resistance:5,000Mohm min.

Materials:
 Insulator:PBT (UL94V-0)
 Contact material:Phosphor Bronze
 Plating:Selective Gold Plated

HOW TO ORDER
 2200SA-39SG-E2X

Empty Pin
 Selective Gold Plating 1u"
 No. Of Position
 Series Number



P.C.B LAYOUT

				DRAWN: Jeremy Liu	GENERAL TOLERANCE: .X=±0.2 .XX=±0.15	 DISPLAY VISIONS ELECTRONIC ASSEMBLY <i>new display design</i>	DESCRIPTION: 1.27MM CENTER SINGLE ROW PCB SOCKET	SIZE A4
				CHECKED: Jerry Chen	UNIT: MM			
				APPROVAL: Mike Wu	SCALE: 10:1	PART NO: EA B254-20		
REV	DATE	FILE	BY		SHEET: 1 / 1			
					PROJECTION:			