














64AT34 SERIES CHART 2

CAT. LISTING								
64AT34-1A		 LOCKED IN THREE POSITIONS	 LOCKED IN CENTER AND EXTREME POSITION (KEYWAY SIDE)	 LOCKED OUT OF CENTER POSITION	 LOCKED IN CENTER POSITION			
64AT34-1B								
64AT34-1D								
64AT34-1E								
64AT34-1F		 LOCKED IN EXTREME POSITION (OPPOSITE KEYWAY)	 LOCKED IN EXTREME POSITION (KEYWAY SIDE)	 LOCKED OUT OF CENTER AND EXTREME POSITION (KEYWAY SIDE)	 LOCKED OUT OF CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)			
64AT34-1G								
64AT34-1H								
64AT34-1J								
64AT34-1K		 LOCKED IN CENTER AND EXTREME POSITION (OPPOSITE KEYWAY)	 LOCKED OUT OF EXTREME POSITION (KEYWAY SIDE)	 LOCKED OUT OF AND INTO EXTREME POSITION (OPPOSITE KEYWAY)	 LOCKED OUT OF EXTREME POSITION (OPPOSITE KEYWAY)			
64AT34-1L								
64AT34-1M								
64AT34-1N								
64AT34-1P	FAA-PMA							
64AT34-3D								
64AT34-3F								
64AT34-3G								
64AT34-5E								
64AT34-5F								
64AT34-5K								
64AT34-5L								
64AT34-5M								
64AT34-5N								
64AT34-7E								
64AT34-7L								
64AT34-7N								
64AT34-514B								
64AT34-514E								
64AT34-514G								
64AT34-514L								
64AT34-514N								
64AT34-514P								

- 1 - UNIT INCLUDES "23SX" TYPE (GOLD CONTACT) BASIC SWITCH (4)
(MEETS REQUIREMENTS OF MIL-PRF-8805)
- 2 - SWITCHES DO NOT NECESSARILY OPERATE SIMULTANEOUSLY
- 3 - PLATED TERMINALS WILL ACCEPT "AMP INC" .058 DIA PIN RECEPTACLES
- 4 - SWITCH NUMBERS STAMPED ON END OF BASIC SWITCHES
- 5 - TERMINAL DESIGNATION STAMPED ON BOTH SIDES OF UNIT
- 6 - DULL FINISH ON LEVER AND BUSHING
- 7 - FLAT WHITE RESILIENT SILICONE (50 DUROMETER APPROX)
- 8 - SUFFIX LETTER MUST BE ADDED FOR DESIRED TYPE TOGGLE LOCKING (SEE
CHART FOR RECOMMENDED LOCKING COMBINATIONS)
- 9 - FOR REPLACEMENT BUTTON SEE MICRO SWITCH CAT. LIST. 15PA90-6W
- 10 - HARDWARE FURNISHED ASSEMBLED WITH SWITCH OR IN PACKET
15PA313-AT PER MIL-PRF-8805
- 11 - REPLACEMENT MOUNTING HARDWARE PACKET 15PA313-AT
- 12 - FOR MANUFACTURING DETAIL SEE THE CORRESPONDING ASSEMBLY DRAWING
FOR EACH LISTING FOR FAA-PMA.

DESIGN UNITS: INCH TOLERANCES UNLESS NOTED: NO PLACE X ± ONE PLACE .X ± 0.030 TWO PLACE .XX ± 0.015 THREE PLACE .XXX ± 0.005 FOUR PLACE .XXXX ± ANGLES ± THIRD ANGLE PROJECTION 	DRAWN	SLB	21JUN82	Honeywell				
	CHECK	CEB	28JUN82					
	THIS DRAWING COVERS A PROPRIETARY ITEM AND IS THE PROPERTY OF HONEYWELL. THIS DRAWING IS NOT TO BE COPIED OR USED WITHOUT THE PERMISSION OF HONEYWELL.			TITLE				
	INTERPRET PER ASME Y14.5M-1994 OTHER HONEYWELL ENGINEERING STANDARDS MAY APPLY			ASSEMBLY - TOGGLE SWITCH				
	RASTER			SIZE	TYPE	DRAWING NAME		REV
			C	I	64AT34 SERIES CHART 2		8	
			SCALE	FULL	WEIGHT .09 LB EST		SHEET 1 OF 1	

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[64AT34-1A](#)