






REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1370008	2013-07-06	Cary	Change Note & Panel Cut-out
C	LEN13A0050	2013-10-15	Raison	Modify Jack PN,Note Panel THK
D	LEN1610156	2016-01-08	Ruru	Change Note




Tapping Use Bottoming Type, Tap #3

Back Shell



Washer
Gasket



Blind-Hole



3.5

Effective Depth of Thread

PE BAG



Note:

* $\varnothing$ Important Dimension

* Waterproof Rate: IP67 Unmated

* Housing: Nylon+GF, BLACK

* RJ45 Jack: Cat 5e, Shield

* Gasket: Silicone, UL 94V-0, Black

* Screw: M3.0x L=8.0mm

* Contact: Phosphor Bronze, Gold Flash

* Screw torsion value range: 1.5~2kgf-cm

* Temperature Range: -40°C to 105°C

* All Parts Should Meet RoHS Compliant.

UNIT:mm		TITLE	RJ45 ODVA,PANEL,REAR LOCK UNMATED WATERPROOF		
TOLERANCE		SCALE	SIZE	SHEET	OF
.X	±0.25	1:1	A4	1	1
.XX	±0.1	REV.	WC-REV.	A.3	
.XXX	±0.05	D		$\varnothing$: Inspection item	
ANGLES	±1°				

Amphenol LTW
安費諾亮泰企業股份有限公司

ITEM NO	ROP-5SRFFH-TSU7001	DRAWN BY	Ruru	DATE	2016-01-08
DWG NO	ROP-5SRFFH-TSU7001	CHECKED BY	Rita	DATE	2016-01-08
CUSTOMER	ALTW	APPROVED BY	Lisa	DATE	2016-01-08

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.