



## Datasheet for part number CA3106E16-10S-B-14-F0

|                                                                                      |
|--------------------------------------------------------------------------------------|
| Our Catalog Part Number: CA3106E16-10S-B-14-F0                                       |
| Our Global Manufacturing Part Number: 121575-2495                                    |
| Brand: Cannon Product Category: Circular Product Line: CA Bayonet Series: CA BAYONET |

| Product Datasheet                                |                                                                                                                       |
|--------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------|
| Bayonet                                          | Connector with bayonet coupling                                                                                       |
| Shell Style                                      | Plug, straight                                                                                                        |
| Endbell Style                                    | Shielded connector with endbell for shielded braids and heat shrinkable boots                                         |
| Gender                                           | Socket                                                                                                                |
| Shell Size                                       | 16                                                                                                                    |
| Contact Arrangement                              | 16-10                                                                                                                 |
| Number of contacts                               | 3 contacts size 25                                                                                                    |
| Contact Type                                     | Metric Crimp                                                                                                          |
| Contact Plating                                  | Hard silver                                                                                                           |
| Contacts included                                | no, delivery without contacts                                                                                         |
| Shielding                                        | yes                                                                                                                   |
| Contact Rating at +20 °C (68 °F)<br>(Size 25/12) | 41 A                                                                                                                  |
| Contact Resistance (Size 25/12)                  | 3 mΩ                                                                                                                  |
| Wire Cross Section                               | 2,0-3,0mm <sup>2</sup>                                                                                                |
| Operating Voltage                                | In case of voltages greater than 50V the connector must be used in accordance with DIN VDE part 410, IEC 60364-4-41.  |
| Insulator Resistance                             | Acc. To VG95319, part 2, test no. 5.12 and VG95210, part 32, test conditions B, standard insulator material > 1000 MΩ |
| Test Voltage                                     | 2000 Vrms                                                                                                             |
| Air and Creepage Paths (Min)                     | 1,1 mm                                                                                                                |
| Ambient Temperature                              | Standard insulator material -55°/+125°C (-67/257°F)                                                                   |
| Safety Provisions                                | IP67 acc. to DIN 40 050 and IP68 (1 bar pressure for 16h)                                                             |
| Salt Spray Resistance                            | 500 hours salt spray resistant                                                                                        |
| Mating Cycles                                    | 500 min                                                                                                               |
| Sep. Force per Contact (Size 25/12)              | 1,5 N                                                                                                                 |
| Gauge                                            | For infos on Gauge please see catalog VG95234, part 1                                                                 |
| Coupling Torque                                  | Closing: 5,5 Nm max / Opening: 0,46 Nm min                                                                            |
| Contact Retention (Size 25/12)                   | 55 N                                                                                                                  |
| Shell Material                                   | Aluminium alloy                                                                                                       |
| Shell Plating                                    | Olive drab chromate over cadmium plating (conductive)                                                                 |
| Insulator and Grommet Material                   | CR-Elastomere                                                                                                         |
| Contact Material                                 | Copper alloy                                                                                                          |
| Harnessing Info: Contact Cross-Section           | <a href="#">See assembly instruction</a>                                                                              |
| Harnessing Info: Insulator Diameter              | <a href="#">See assembly instruction</a>                                                                              |
| Wire Stripping (Size 25/12)                      | 6,2 mm                                                                                                                |
| General Info                                     | All tests in accordance with VG95319 and/or if applicable with VG95210                                                |

Specifications and dimensions subject to change.