

FCB-205-0220M=M83536/2-020M

✓ ACTIVE

CII | CII FCB-205 Series

TE Part # 4-1617758-5


TE Internal #: FCB-205-0220M

Mil-Spec: [M83536/2-020M]

[View on TE.com >](#)



Relays, Contactors & Switches > Relays > Mil-Aero Relays > Mid-Range Relays



Contact Arrangement: 2 Form C, DPDT, 2 C/O

Coil Suppression Diode: With

Auxiliary Contacts: Without

Terminal Plating: Tin-Lead

Contact Current Rating: 5 A

Features

Product Type Features

Enclosure Type	Hermetically Sealed
Terminal Configuration	Solder Hook
Product Type	Relay
Relay Type	Military/Aerospace Mid-Range

Electrical Characteristics

Vibration	30G's, 70 – 3000Hz
Shock	200G's, 6ms
Coil Suppression Diode	With
Coil Voltage Rating	28 VDC
Coil Resistance	500 Ω
Back EMF Suppression	With
Coil Magnetic System	Polarized, Monostable
Actuating System	DC

Contact Features

Contact Arrangement	2 Form C, DPDT, 2 C/O
Auxiliary Contacts	Without
Terminal Plating	Tin-Lead
Contact Current Rating	5 A
Contact Base Material	Silver Cadmium Oxide



Mechanical Attachment

Mounting Type	No Brackets
---------------	-------------

Usage Conditions

Operating Temperature Range	-70 – 125 °C
-----------------------------	--------------

Product Compliance


For compliance documentation, visit the product page on TE.com>

EU RoHS Directive 2011/65/EU	Not Compliant
EU ELV Directive 2000/53/EC	Not Compliant
China RoHS 2 Directive MIIT Order No 32, 2016	Restricted Materials Above Threshold
EU REACH Regulation (EC) No. 1907/2006	Current ECHA Candidate List: JAN 2019 (197) Candidate List Declared Against: JAN 2019 (197)
Halogen Content	Not Yet Reviewed for halogen content
Solder Process Capability	Not lead free process capable

Product Compliance Disclaimer

This information is provided based on reasonable inquiry of our suppliers and represents our current actual knowledge based on the information they provided. This information is subject to change. The part numbers that TE has identified as EU RoHS compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, mercury, PBB, PBDE, DBP, BBP, DEHP, DIBP, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2011/65/EU (RoHS2). Finished electrical and electronic equipment products will be CE marked as required by Directive 2011/65/EU. Components may not be CE marked. Additionally, the part numbers that TE has identified as EU ELV compliant have a maximum concentration of 0.1% by weight in homogenous materials for lead, hexavalent chromium, and mercury, and 0.01% for cadmium, or qualify for an exemption to these limits as defined in the Annexes of Directive 2000/53/EC (ELV). Regarding the REACH Regulations, TE’s information on SVHC in articles for this part number is still based on the European Chemical Agency (ECHA) ‘Guidance on requirements for substances in articles’(Version: 2, April 2011), applying the 0.1% weight on weight concentration threshold at the finished product level. TE is aware of the European Court of Justice ruling of September 10th, 2015 also known as O5A (Once An Article Always An Article) stating that, in case of ‘complex object’, the threshold for a SVHC must be applied to both the product as a whole and simultaneously to each of the articles forming part of its composition. TE has evaluated this ruling based on the new ECHA “Guidance on requirements for substances in articles” (June 2017, version 4.0) and will be updating its statements accordingly.

Compatible Parts



TE Part # 7-1617760-7
[FCB-405-0617M=M83536](#)
[/6-017M](#)



Also in the Series | CII FCB-205 Series



Mid-Range Relays(47)


Customers Also Bought



TE Part #1059651-1
4557 5368 02




TE Part #1410714-2
MULTIGIG RT GUIDE 7.2 MM



TE Part #1484244-1
ADAPTER, TCN PLUG TO N JACK 3682 2311 02



TE Part #3-1617515-0
3SBC1793A2=M39016/13-101M



TE Part #65053-234
ELEC MODULE



TE Part #DTS24W21-41SB
RECP ASSY



TE Part #2-1617802-4
FCA-150-KU4=50 AMP 1PST/NO DM RELAY



TE Part #9-1617805-3
FCA-150-KX4=50 AMP 1PST/NO DM RELAY



TE Part #1617756-7
FCA-410-CY9



TE Part #070539-000
TXR21AB90-1608AI

Documents

Product Drawings
FCB-205-0220M=M83536/2-020M

English

Datasheets & Catalog Pages
5-1773450-5_sec5_FCB-205

English

