





2-1520237-4 Product Details



2-1520237-4

TE Internal Number: 2-1520237-4



Active

[View 3D PDF](#)

Power Toggle Switches

 Always EU RoHS/ELV Compliant (Statement of Compliance)

Product Highlights:

- Double Pole - Single Throw Configuration (Pole-Throw)
- Toggle Length = 16.28 mm
- Toggle Style = Baton
- Bushing Length = 8.74 mm
- Termination Type = Screw-In Terminal

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

[Add to My Part List](#) [Request Sample](#) [Find Similar Products](#) [Buy Product](#)

Documentation & Additional Information

Product Drawings:

- [DIM'S FOR DBL. POLE TOOL HANDLE SW. FOR EUROPEAN USE](#) (PDF, English)

Catalog Pages/Data Sheets:

- None Available

Product Specifications:

- None Available

Application Specifications:

- None Available

Instruction Sheets:

- None Available

CAD Files: (CAD Format & Compression Information)

- [2D Drawing](#) (DXF, Version E)
- [3D Model](#) (IGES, Version E)
- [3D Model](#) (STEP, Version E)

[List all Documents](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Electrical Characteristics:

- UL/CSA 125V Current Rating (A) = 8
- UL/CSA 250V Current Rating (A) = 6
- UL/CSA 125V Horse Power Rating (hp) = 0.50
- UL/CSA 250V Horse Power Rating (hp) = 0.50

Termination Features:

- Termination Type = Screw-In Terminal

Dimensions:

- Toggle Length (mm [in]) = 16.28 [0.641]
- Bushing Length (mm [in]) = 8.74 [0.344]

Housing Features:

- Toggle Style = Baton

Configuration Features:

- Configuration (Pole-Throw) = Double Pole - Single Throw

Industry Standards:

- [RoHS/ELV Compliance](#) = RoHS compliant, ELV compliant
- [Lead Free Solder Processes](#) = Not relevant for lead free process
- RoHS/ELV Compliance History = Always was RoHS compliant

Other:

- Brand = TE Connectivity

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)
[Terms & Conditions](#)
[Privacy Policy](#)
[AODA Accessibility Policy](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



