

Coaxial Cable Connector 21_SMA-50-6-1/12-_N

Description

Straight cable jack

Interface standards
MIL-STD-348A/310



Technical Data

Electrical Data

Impedance	50 Ω		
Interface frequency max.	18 GHz		
Frequency range	DC to 6 GHz	6 to 11 GHz	11 to 18 GHz
Return loss	28.3 dB	24.9 dB	22.6 dB

Mechanical Data

Centre contact	plugged
Outer contact	clamped

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	Nickel Plating
Body	Brass	Nickel Plating
Other body part	Stainless Steel	
Insulator	PTFE (Polytetrafluoroethylene)	
Gasket	VMQ (Silicone rubber)	

Related Documents

Outline drawing	DOU-00323343
Assembly instruction	DOC-0000723577

Ordering Information

Single package	21_SMA-50-6-1/12-_NE
----------------	----------------------

Additional Information

Suitable cables	EACON_6C
-----------------	----------