

SERIES 29

FEATURES


- Quick Connect/Disconnect
- Only 7/8" Above Board Height
- Standard, Insulated, or Banana Plug Styles
- High Temperature Spring Style
- Color-Coded Caps with Optional Additional Colors



DESCRIPTION

Press button and put lead in slot and release. Spring pressure assures firm, positive contact.

DIMENSIONS In Inches (and millimeters)



SPECIFICATIONS

Rating Criteria

Rating: At 120 Vdc, 20A continuously, with a maximum temperature rise of 20°C.

Materials and Finishes

External Metal Parts: Nickel-plated brass

Spring: Tinned music wire

Button Caps: Polyethylene

Washers (29-104): Black thermoset plastic

High Temperature Spring: Stainless steel

OPTIONS

Green or White Caps

Gold plate finish: Available on all but Banana Plug styles.

ORDERING INFORMATION

Description	Part Number
Standard, without cap	29-110
Standard, with red cap	29-100 RED
Standard, with black cap	29-100 BLK
High temperature standard, without cap	29-125
Insulated, with black cap	29-104 BLK
Insulated, with red cap	29-104 RED
Banana plug, with black cap	29-101 BLK
Banana plug, with red cap	29-101 RED

Available from your local Grayhill Distributor.

For prices and discounts, contact a local Sales Office, an authorized local Distributor or Grayhill.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Grayhill:

[29-100 BLK](#) [29-100 GRN](#) [29-100 RED](#) [29-100 WHT](#) [29-101 BLK](#) [29-101 RED](#) [29-104 BLK](#) [29-104 GRN](#) [29-104 RED](#) [29-104 WHT](#)