



General ordering data

Order No.	1969990000
Part designation	BCF 3.81/07/180 SN SW
Version	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
EAN	4032248679577
Qty.	50 pc(s).

Classifications

eClass 5.1	27-26-07-04
------------	-------------

Similar products

Order No.	Part designation	Version
1969090000	BCF 3.81/02/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1969890000	BCF 3.81/02/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1969280000	BCF 3.81/02/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 2, 180°, Box
1969100000	BCF 3.81/03/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1969920000	BCF 3.81/03/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1969290000	BCF 3.81/03/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 3, 180°, Box
1969110000	BCF 3.81/04/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1969950000	BCF 3.81/04/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box
1969300000	BCF 3.81/04/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 4, 180°, Box

1969970000	BCF 3.81/05/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1969120000	BCF 3.81/05/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1969480000	BCF 3.81/05/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 5, 180°, Box
1969980000	BCF 3.81/06/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1969130000	BCF 3.81/06/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1969490000	BCF 3.81/06/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 6, 180°, Box
1969140000	BCF 3.81/07/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1969500000	BCF 3.81/07/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 7, 180°, Box
1969150000	BCF 3.81/08/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1970000000	BCF 3.81/08/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1969510000	BCF 3.81/08/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 8, 180°, Box
1969160000	BCF 3.81/09/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1970040000	BCF 3.81/09/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1969530000	BCF 3.81/09/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 9, 180°, Box
1969170000	BCF 3.81/10/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1970130000	BCF 3.81/10/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1969550000	BCF 3.81/10/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 10, 180°, Box
1969180000	BCF 3.81/11/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1970170000	BCF 3.81/11/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1969600000	BCF 3.81/11/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 11, 180°, Box
1969190000	BCF 3.81/12/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1970190000	BCF 3.81/12/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1969620000	BCF 3.81/12/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 12, 180°, Box
1969200000	BCF 3.81/13/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1970200000	BCF 3.81/13/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box
1969650000	BCF 3.81/13/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 13, 180°, Box

1969210000	BCF 3.81/14/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1970210000	BCF 3.81/14/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1969680000	BCF 3.81/14/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 14, 180°, Box
1969220000	BCF 3.81/15/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1970220000	BCF 3.81/15/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1969710000	BCF 3.81/15/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 15, 180°, Box
1969230000	BCF 3.81/16/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1970230000	BCF 3.81/16/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1969740000	BCF 3.81/16/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 16, 180°, Box
1969240000	BCF 3.81/17/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1970240000	BCF 3.81/17/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1969760000	BCF 3.81/17/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 17, 180°, Box
1969250000	BCF 3.81/18/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1970250000	BCF 3.81/18/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1969790000	BCF 3.81/18/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 18, 180°, Box
1969260000	BCF 3.81/19/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1970280000	BCF 3.81/19/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1969850000	BCF 3.81/19/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 19, 180°, Box
1969270000	BCF 3.81/20/180 SN OR	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box
1970290000	BCF 3.81/20/180 SN SW	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box
1969880000	BCF 3.81/20/180 SN GN	Leiterplattensteckverbinder, Female connectors, Push In, Clamping range, max.: 1.5 mm ² , Pitch: 3.81 mm, No. of poles: 20, 180°, Box