









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313A0337	2013-10-23	Raison	Modify Jack,Note
C	LEN1440186	2014-04-19	Tom_gu	Change D Cut




Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate : IP67 Mated
- * Housing : Nylon+GF,UL 94V-0,BLACK
- * Screw Nut : Nylon+GF,BLACK
- * $\triangle$ Gasket : Silicone,UL 94V-0,Gray.
- * PCB: FR-4
- * Jack : PBT Polyester UL 94V-0
- * $\triangle$ Ground Terminal:Brass,Tin Plated,Thickness:0.4mm
- * $\triangle$ Use without Waterproof cap or Dust cap
For Panel Thickness Max: 4.2mm
- * Use with Waterproof cap or Dust cap
For Panel Thickness Max: 3.0mm
- * $\triangle$ Screw torsion value range: 8~12kgf-cm



Recommended Panel Cut-out
Rear View



UNIT:mm				TITLE RJ45,C SIZE,MATED WATERPROOF ADD GROUND WIRE			Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO RCP-5SPFFH-TCM7002		DRAWN BY Tom_gu		DATE 2014-04-19				
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°									SCALE 1:1		SIZE A4		SHEET 1 OF 1		DWG NO RCP-5SPFFH-TCM7002		CHECKED BY Tony
				REV. C		WC-REV. B.3			QC:Inspection item		CUSTOMER ALTW		APPROVED BY Victor		DATE 2014-04-19		

Amphenol LTW
安費諾亮泰企業股份有限公司

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.