









THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.

REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LEN1370010	2013/07/06	Cary	Change Note & Panel Cut-out
C	LEN1610153	2016/01/08	Ruru	Change Note
D	LEN1670656	2016/07/19	Feng_Li	Modify Gasket Shape



- Note:
- * $\varnothing$ Important Dimension
 - * Waterproof Rate: IP67 (Mated Waterproof)
 - * Housing: Nylon+GF, BLACK
 - * RJ45 Jack: Cat 5e, Shield
 - * Gasket: Silicone, UL 94V-0, Black
 - * Screw: M3.0x L=8.0mm
 - * Contact: Phosphor Bronze, Gold Flash Over Nickel
 - * Screw torsion value range: 1.5~2kgf-cm
 - * Temperature Range: -40°C to 105°C
 - * All Parts Should Meet RoHS Compliant

UNIT:mm		TITLE	RJ45 ODVA,PANEL,DOUBLE LOCK		
TOLERANCE		SCALE	1:1	SIZE	A4
.X	±0.25	REV.	D	WC-REV.	B.5
.XX	±0.1	SHEET 1 OF 1			
.XXX	±0.05	QC: Inspection item			
ANGLES	±1°				

Amphenol LTW		ITEM NO	ROP-5SPFFH-TSM7001	DRAWN BY	Feng_Li	DATE	2016-07-19
安費諾亮泰企業股份有限公司		DWG NO	ROP-5SPFFH-TSM7001	CHECKED BY	Jinhai	DATE	2016-07-19
		CUSTOMER	ALTW	APPROVED BY	Jerry	DATE	2016-07-19