

## R 15-egw



Image is for illustration purposes only. Please refer to product description.

Part number	09 15 000 0122
Specification	R 15-egw
HARTING eCatalogue	<a href="https://b2b.harting.com/09150000122">https://b2b.harting.com/09150000122</a>

### Identification

Category	Hoods/Housings
Series	R 15
Type of hood/housing	Screw mounted housing
Description of hood/housing	Angled

### Version

Locking type	Screw locking
--------------	---------------

### Technical characteristics

Limiting temperature	-40 ... +125 °C
Note on the limiting temperature	For use as a connector according to IEC 61984.
Degree of protection acc. to IEC 60529	IP65

### Material properties

Material (hood/housing)	Aluminium
Material (seal)	NBR
RoHS	compliant with exemption
RoHS exemptions	6(c): Copper alloy containing up to 4 % lead by weight
ELV status	compliant with exemption
China RoHS	50
REACH Annex XVII substances	Not contained
REACH ANNEX XIV substances	Not contained
REACH SVHC substances	Yes

## Material properties

REACH SVHC substances	Lead
ECHA SCIP number	6fb545c1-f438-46c2-b07a-8552e7e5a3d7
California Proposition 65 substances	Yes
	Lead
California Proposition 65 substances	Nickel
	Naphthalene

## Commercial data

Packaging size	10
Net weight	87.54 g
Country of origin	Germany
European customs tariff number	85389099
GTIN	5713140021624
ETIM	EC003556
eCl@ss	27440224 Shell for circular connectors