



1 Products

1-1

Product No.	PO51-J-1.5W(40)
HRS No.	330-0201-9 40
Status	In Production
RoHS	Yes
Series	PO51
Category	Coaxial Connectors
No. of Positions	N/A
Contact Mating Area Plating	Gold
Contact Gender	Female
Connector Type	Cable
PCB Mount Type	N/A
Current Rating(Amps)(Max.)	N/A
Impedance (ohm)	50
Frequency (GHz)(Min)	0
Frequency (GHz)(Max)	1
V.S.W.R. (Max)	1.2
Termination Style	Soldering
Temperature (deg C)	-55 to 85
Mating/Unmating Cycles	500
Applicable Cable	1.5DQEW
Generic Name	N/A
Selling Unit	1pcs.(1pcs.)
General Description	Jack; Pushpull lock
Inquiry	
Similar Products	N/A
e-Commerce	
Product No.	PO51-J-1.5W(40)
HRS No.	330-0201-9 40

1-1

 Terms of Service  RoHS