

Coaxial Cable Connector 21_N-50-3-11/133_N

Description

Straight cable jack

Interface standards

IEC 61169-16_MIL-STD-348A/304_CECC 22210



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	soldered
Outer contact	soldered
Weight	0.0378 kg

Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Copper Beryllium Alloy	Gold Plating (Nickel underplated)
Outer contact	Brass	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	

Related Documents

Catalogue drawing	DOU-00007451
Assembly instruction	DOC-0000350737

Ordering Information

Single package	21_N-50-3-11/133_NE
----------------	---------------------

Additional Information

Suitable cables	EZ_141_TP_M17
-----------------	---------------