

**Mallory Sonalert Products, Inc.**

Part #:

SBS12GLPC**Sales Outline Drawing**


Revision:

E

Specifications:	cUL Recognized to IEC60601-1-8 AMD2:2020 Any Melody - Low Priority Only
Sound Level Category:	Extra Loud
Mode of Operation:	Low Priority Alarm - 2 beeps repeating every 20 sec
Voltage Rating:	9 to 12 VDC
Frequency:	150 to 4000 Hz
Loudness @ 10cm:	95 to 105 dB(A) Typ.
Average Current Draw:	<300mA Typ.
Ipk Current*:	400mA
Housing Material:	ABS 777D Plastic Resin, Black
Storage Temperature:	-40° to +85° C
Operating Temperature:	-30° to +65° C
Weight Typical:	1.1 oz (32g)
Options:	Please contact factory.
Condition by wave solder (°C)	260 ± 5 within 5 sec
Condition by hand solder (°C)	350 ± 20 within 5 sec

Dimensions: Inches (mm)**cUL Recognized****ROHS Compliant**

PATENT NUMBER: 7880593



*Ipk = Instantaneous Peak

tolerances:

 ± 0.01 [± 0.3] ± 0.005 [± 0.1]