

Coaxial Cable Connector 11_QMA-50-2-2/133_N

Description

Straight cable plug

Interface standards
QMA QLF compliant



Technical Data

Electrical Data

Impedance	50 Ω
Interface frequency max.	18 GHz

Mechanical Data

Centre contact	crimped
Outer contact	crimped
Weight	0.0041 kg

Environmental Data

Operating temperature	-40 °C to 85 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

Material Data

Piece Parts	Material	Surface Plating
Centre contact	Brass	SUCOPRO Plating
Outer contact	Bronze	SUCOPLATE (R) Plating
Body	Brass	SUCOPLATE (R) Plating
Insulator	PFA / PTFE	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

Related Documents

Outline drawing	DOU-00005827
Catalogue drawing	DOU-00005829
Assembly instruction	DOC-0000183265

Ordering Information

Bulk 100 pcs package	11_QMA-50-2-2/133_NH
Single package	11_QMA-50-2-2/133_NE

Additional Information

Suitable cables	RG_316_/U, ENVIROFLEX_316, RG_188_A/U, RG_174_/U
-----------------	--