

TPF11CGPC0 Product Details



Pushbutton Switches

[Not EU RoHS or ELV Compliant \(Find RoHS Compliant Alternates\)](#)

TPF11CGPC0

(6-1437572-8)

TE Internal Number: 6-1437572-8


[View all Features](#)
[Live Product Chat](#)

Quick Links

[Check Pricing & Availability](#)
[Search for Tooling](#)
[Product Feature Selector](#)
[Contact Us About This Product](#)
[!\[\]\(1f56542a42e2413e44a2b2023033aa2e_img.jpg\) Add to My Part List](#) [!\[\]\(f68284289fe27ddc7c7b21cde471c330_img.jpg\) Request Sample](#) [!\[\]\(422d5b9f9ba3e618ff84327faa03f0b1_img.jpg\) Find Similar Products](#) [!\[\]\(1f62ea705694bcbeaffcca6e2ab5056e_img.jpg\) Buy Product](#)

Documentation & Additional Information	
<p>Product Drawings:</p> <ul style="list-style-type: none"> None Available <p>Catalog Pages/Data Sheets:</p> <ul style="list-style-type: none"> ALCOSWITCH PRODUCTS (PDF, English) <p>Product Specifications:</p> <ul style="list-style-type: none"> None Available <p>Application Specifications:</p> <ul style="list-style-type: none"> None Available <p>Instruction Sheets:</p> <ul style="list-style-type: none"> None Available <p>CAD Files:</p> <ul style="list-style-type: none"> None Available 	<p>Additional Information:</p> <ul style="list-style-type: none"> Product Line Information <p>Related Products:</p> <ul style="list-style-type: none"> Tooling

[List all Documents](#)

Product Features (Please use the Product Drawing for all design activity)	
<p>Product Type Features:</p> <ul style="list-style-type: none"> Product Type = Switch - Mechanical Tactile = No Configuration (Pole-Throw) = Single Pole - Single Throw Mount Angle = Vertical Termination Type = Printed Circuit Actuator Style = Round Comment = No center terminal <p>Electrical Characteristics:</p> <ul style="list-style-type: none"> Contact Rating = 0.4VA <p>Body Related Features:</p> <ul style="list-style-type: none"> Series = TPF Mount Style = Through-Hole Actuator Length (mm [in]) = 4.01 [0.158] Actuator Profile = Extended Actuator Color = Black Bushing Diameter = 1/4-40 Case Material = Polyester Actuator Material = Polyamide <p>Contact Related Features:</p> <ul style="list-style-type: none"> Contact Plating = Gold over Nickel <p>Housing Related Features:</p> <ul style="list-style-type: none"> Process Sealed = No Low Profile = No Bushing Style = Threaded 	<p>Configuration Related Features:</p> <ul style="list-style-type: none"> Operating Function = Normally Open, Momentary Ganged = No ESD Grounding Terminal = Without Actuator Force (g [oz]) = 50.00 – 400.00 [1.770 – 14.120] Number of Actuators = Single Illuminated = No Dust Proof = No Support Bracket = Without Snap Action = Without <p>Industry Standards:</p> <ul style="list-style-type: none"> RoHS/ELV Compliance = Not ELV/RoHS compliant Lead Free Solder Processes = Wave solder capable to 240°C, Wave solder capable to 260°C, Wave solder capable to 265°C <p>Conditions for Usage:</p> <ul style="list-style-type: none"> Temperature Rating = High <p>Packaging Related Features:</p> <ul style="list-style-type: none"> Packaging Method = Loose Piece <p>Other:</p> <ul style="list-style-type: none"> Brand = Alcoswitch

Corporate Information

[Who We Are](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)
[Careers](#)

Quick Links

[Check Distributor Inventory](#)
[Cross Reference](#)
[Find Documents & Drawings](#)
[Product Compliance Support Center](#)
[Site Map](#)

Customer Support

[Email or Chat with Us](#)
[Find a Phone Number](#)
[Search Knowledge Base](#)
[Manage Your Account](#)