









REV.	ECN NO.	DATE	SIGN	DESCRIPTION
B	LE313A0310	2013-09-07	Raison	Modify Jack,Note.Change H Cut
C	LEN1440099	2014-04-04	Tom_gu	Change H Cut To D Cut




Note:

- * $\varnothing$ Important Dimension
- * Waterproof Rate : IP67 Mated
- * Housing : Nylon+GF,UL 94V-0,BLACK
- * Screw Nut : Nylon+GF,BLACK
- * $\triangle$ Gasket : Silicone,UL 94V-0,Gray.
- * PCB: FR-4
- * Jack : PBT Polyester UL 94V-0
- * $\triangle$ Ground Terminal:Brass,Tin Plated,Thickness:0.4mm
- * $\triangle$ Use without Waterproof cap or Dust cap
For Panel Thickness Max: 4.2mm
- * Use with Waterproof cap or Dust cap
For Panel Thickness Max: 3.0mm
- * $\triangle$ Screw torsion value range: 8~12kgf-cm



Recommended
Panel Cut-out
Rear View



UNIT:mm		TITLE RJ45,C SIZE,MATED WATERPROOF ADD GROUND WIRE		Amphenol LTW 安費諾亮泰企業股份有限公司		ITEM NO RCP-5SPFFV-SCM7002	DRAWN BY Tom_gu	DATE 2014-04-04
TOLERANCE .X ±0.25 .XX ±0.1 .XXX ±0.05 ANGLES ±1°		SCALE 1:1	SIZE A4			DWG NO RCP-5SPFFV-SCM7002	CHECKED BY Tony	DATE 2014-04-04
REV. C		WC-REV. B.4	$\varnothing$ Inspection item		CUSTOMER ALTW	APPROVED BY Victor		DATE 2014-04-04

THIS DOCUMENT IS SUBJECT TO CHANGE WITHOUT NOTICE. IT IS CONFIDENTIAL AND A PROPERTY OF Amphenol LTW. DISCLOSURE TO THIRD PARTY HAS TO BE AUTHORIZED BY Amphenol LTW.