



REV. C



IN PROCESS



PACKAGING VIEW


DO NOT SCALE
FROM THIS PRINT**PROPRIETARY NOTE**

THIS DOCUMENT CONTAINS INFORMATION
CONFIDENTIAL AND PROPRIETARY TO
SAMTEC INC. AND SHALL NOT BE
REPRODUCED OR TRANSFERRED TO
OTHER DOCUMENTS OR DISCLOSED TO
OTHERS OR USED FOR ANY PURPOSE
OTHER THAN THAT FOR WHICH IT WAS
OBTAINED WITHOUT THE EXPRESSED
WRITTEN CONSENT OF SAMTEC INC.

DIMENSIONS ARE IN INCHES		UNLESS OTHERWISE NOTED	TOLERANCES ARE:
ONE PLACE DECIMALS $\pm .1[2.5]$	THREE PLACE DECIMALS $\pm .005[.127]$	ANGLES	$\pm 2^\circ$
TWO PLACE DECIMALS $\pm .01[.25]$	FOUR PLACE DECIMALS $\pm .0020[.051]$		

TITLE: SQT SOCKET
2 MM
SINGLE ROW ASM

DWG NO:
SQT-1XX-01-X-S-VS
SHEET 1 OF 1





SQT-1XX-01-X-S-VS

POSITION SPECIFICATION
-02 THRU -50 (PER ROW)

PLATING SPECIFICATION

-F: FLASH SELECTIVE GOLD
-L: LIGHT SELECTIVE GOLD
-G: GOLD
-S: SELECTIVE GOLD
-H: HEAVY GOLD

**NOTES:**

- DIM TO BE MEASURED AT BEND RADIUS.
- POSITIONS 05 THRU 50 TO BE PACKAGED
IN PT-1-24-05-15 USE TUBE PLUG TP-24;
POSITIONS 02 THRU 04 TO BE LAYER PACKAGED.
- MAX FLASH ALLOWED .003 [.08]
- FOR ODD POSITIONS, LOSE ONE POSITION PER CUT,
FOR EVEN POSITIONS, LOSE TWO POSITIONS PER CUT.
- Ⓢ REPRESENTS A CRITICAL DIMENSION.

MATERIAL:
VECTRA E130
COLOR: BLACK
10% MAX REGRIND
MAX BOW: .003 IN/IN

MAX FLASH ALLOWED:
.003 [.08]

samtec

MISC\MKTG\
SQT-SV-ASM

520 PARK EAST BLVD. NEW ALBANY, INDIANA 47150
PHONE (812) 944-6733 P.O. BOX 1147
CODE 55322

MADE BY:
D JONES 10-31-96

SQT-1XX-01-X-S-VS
SHEET 1 OF 1