



6368062-9 Product Details



6368062-9

PCB Mounted Jacks - Single Port, Multi-port and Stacked

Not reviewed for RoHS Compliance

Product Highlights:


- Connector
- Preloaded
- Stacked Port Configuration
- 2 x 4 Jack Configuration
- Jack Type = RJ45

[View all Features](#)

Quick Links

- ▶ [Pricing & Availability](#)
- ▶ [Search for Tooling](#)
- ▶ [Product Feature Selector](#)
- ▶ [Contact Us About This Product](#)

TE Internal Number: 6368062-9



[Request Sample](#)



[Find Similar Products](#)



[Buy Product](#)

Documentation & Additional Information

Documents are temporarily unavailable. We are working hard to correct the problem. Please try again later.

Additional Information:

- [Product Line Information](#)

Related Products:

- [Tooling](#)

Product Features (Please use the Product Drawing for all design activity)

Product Type Features:

- Product Type = Connector
- [Jack Type](#) = RJ45
- [PCB Mounting Orientation](#) = Side Entry (Right Angle)
- [PCB Mount Style](#) = Through Hole
- [Performance Category](#) = Cat 5e
- [LED](#) = With
- [Grounding Options](#) = Panel Ground and PCB Ground
- [Panel Stops](#) = Without
- [Keyed](#) = No
- [Profile](#) = Very Low; Offset - Over Hangs PCB
- [Color](#) = Black

Mechanical Attachment:

- [Panel Mount Retention](#) = Without

Termination Features:

- [Termination Method to PC Board](#) = Through Hole - Press Fit
- [Grounding Clips](#) = Without

Dimensions:

- [PCB Tail Length \(mm \[in\]\)](#) = 4.35 [0.171]
- [PCB Thickness, Recommended \(mm \[in\]\)](#) = 1.57 [0.062]

Body Features:

- [Inverted Jack Face](#) = No
- [Shield Plating](#) = Tin over Copper
- [Shield Material](#) = .010 [0.25] Copper Alloy
- [Grounding Tab Plating](#) = Tin over Copper

Contact Features:

- [Solder Tail Contact Plating](#) = Tin over Nickel
- [Contact Plating, Mating Area, Material](#) = Gold (50)
- [Contact Base Material](#) = Phosphor Bronze
- [PCB ACTION PIN Grounds](#) = Without

Housing Features:

- [Housing Material](#) = PBT - GF
- [Housing Color](#) = Black

Configuration Features:

- [Preloaded](#) = Yes
- [Port Configuration](#) = Stacked
- [Jack Configuration](#) = 2 x 4
- [Number of Positions](#) = 8
- [Shielded](#) = Yes
- [Number of Contacts Loaded](#) = 8

Industry Standards:

- [RoHS/ELV Compliance](#) = Not reviewed for ELV/RoHS compliance
- [Lead Free Solder Processes](#) = Not reviewed for lead free solder process
- [UL Flammability Rating](#) = UL 94V-0

Identification Marking:

- [LED Color; Top Left](#) = Green
- [LED Color; Top Right](#) = Yellow
- [LED Color; Bottom Left](#) = Green
- [LED Color; Bottom Right](#) = Yellow

Product Availability:

- [Region](#) = Asia, North America

Other:

- [Brand](#) = AMP

Corporate Information

[About TE](#)
[Investors](#)
[News Room](#)
[Supplier Portal](#)

Quick Links

[Distributor Inventory](#)
[Product Cross Reference](#)
[Documents & Drawings](#)
[Product Compliance Support Center](#)

Customer Support

[Email or Chat With Us](#)
[Find a Phone Number](#)
[Knowledge Base](#)
[Manage Your Account](#)

Keep Me Informed



