

## Coaxial Cable Connector 11\_N-50-10-5/103\_U

### Description

Straight cable plug

Interface standards

IEC 61169-16\_MIL-STD-348A/304\_CECC 22210



### Technical Data

#### Electrical Data

Impedance	50 $\Omega$
Interface frequency max.	11 GHz
Frequency range	DC to 3 GHz
Return loss	30 dB

#### Mechanical Data

Centre contact	plugged
Outer contact	crimped
Weight	0.0378 kg

#### Environmental Data

Operating temperature	-65 °C to 165 °C
2011/65/EU (RoHS - including 2015/863 and 2017/2102)	compliant

#### Material Data

Piece Parts	Material	Surface Plating
Centre contact	Bronze	Gold Plating (without Nickel underplating)
Outer contact	Brass	Silver Plating
Body	Brass	Silver Plating
Insulator	PFA / PTFE	
Coupling nut	Brass	SUCOPLATE (R) Plating
Gasket	VMQ (Silicone rubber)	
Crimp ferrule	Copper	SUCOPLATE (R) Plating

### Related Documents

Outline drawing	DOU-00008111
Catalogue drawing	DOU-00008113
Assembly instruction	DOC-0000182194

### Ordering Information

Bulk 20 pcs package	11_N-50-10-5/103_UV
---------------------	---------------------

### Additional Information

Suitable cables	S_10172_B-11, S_10162_B-11
-----------------	----------------------------