





Product No: DS868MCS0058

REV	DESCRIPTION	DWN	DATE	APPROVEN
A	FIRST ISSUE	XIEFENG	2022/06/15	Mr.chen



Material and specifications

Coupling	Threaded coupling
Shell material	Brass with Nickel Plate
Insert material	bakelite
Contact material	copper Silver Plate/Nickel
Termination	Solder
Mating cycle	500
Cable diameter	-20℃ +85℃

Technology parameter						
NO.of contacts	2	3	4	5	6	7
Rated current (A)	5	5	5	5	5	5
Operation limit voltage(AC.V.rms)	200	125	125	125	125	125
Withstanding voltage(AC.V.rms)1 minute	1500	1500	1500	1500	1500	1500
Insulation resistance(mΩ)	2000	2000	2000	2000	2000	2000
Contact resistance (mΩ)	5	5	5	5	5	5


NOTE:

DRAWN:	DATE:
XIEFENG	22/06/15
CHECKED:	
APPROVALS:	

Tolerance

UNLESS OTHERWISE SPECIFIED
TOLERANCES FOR DIMENSIONS ARE
0.5-8MM±0.10MM
8-30MM±0.15MM
30-120MM±0.20MM

VIEW



UNIT

MM

SCALE

1 : 1

DOSIN

-RF CONNECTOR

DOSIN INDUSTRIAL(HK)CO.,LTD

东莞市德索五金电子有限公司

Dongguan Dosin Hardware Electronics Co.,Ltd.

Name: GX12 MALE CONNECTOR

Product NO. DS868MCS0058

CAD FILE

H/companydrawings/BD

Web: http://www.dosinconn.com
dosin2005@dosin-china.com
E-mail: dosin2005@163.com
Tel: (0086)769-81153906
Fax: (0086)769-81875836REV
A

SHEET: 1 OF 1