

FED. MFG. CODE 91929

IPB544

CHARACTERISTICS	ELECTRICAL DATA	SCALE FULL
OPERATING FORCE ----- 2 LBS MAX	CONTACT ARRANGEMENT S P D T	DO NOT SCALE PRINT
OVERTRAVEL FORCE ----- 2.5 LBS MAX	30 VOLTS DC RATING INDUCTIVE -----SEA LEVEL----- 3 AMP RESISTIVE ----- SEA LEVEL----- 5 AMP	UNLESS OTHERWISE NOTED
RELEASE FORCE ----- 2 OZ MIN		DIMENSIONS ARE IN INCHES
OVERTRAVEL ----- .100 MIN		TOLERANCES ARE:
DIFFERENTIAL TRAVEL ----- .031 MAX		ONE PLACE (.0) ±.030 TWO PLACE (.00) ±.015 THREE PLACE (.000) ±.005 ANGLES ±
		WEIGHT

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Honeywell:](#)

[1PB544](#)