







Recommended P.C.B Layout(Top Side)
(PCB BOARD TOLERANCE±0.05)




SPECIFICATIONS

Rated Current:1.5AMP
Contact Resistance:20mΩ Max
Withstand Voltage:500V AC/DC
Insulation Resistance:1000MΩ Min
Operation Temperature:-40°C to +105°C

Contact Material:Brass
Contact Plating:Au or Sn Over Ni
Insulator Material:Polyester(UL94V-0)
Standard: PA6T
Max.Processing Temp: 230°C for 30-60 seconds
(260°C for 10 seconds)



P = With Post



默认 = W/O Post

Ordering Information

PM 200 - * - N - S - * - ** - * - P

No. of Rows
1=Single Row
2=Dual Row

No. of Pins
2-40Pin

Type
Z=直针
R=弯针
S=立轴
W=弯轴

Length
(mm)

Contact Plating
G0:Gold Flash
G1:1u" Gold
G2:3u" Gold
G3:5u" Gold
G4:10u" Gold
G5:15u" Gold
G6:30u" Gold
S0:Gold Flash/Tin
S1:Tin

R=Reel
+Cap
(带料)

Post
(带柱)

			GENERAL TOLERANCE		制 图	深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM	TOL	审 核				
			X. X	±0.30	批 准	产品名称	2.00双排 排母 贴片 编带+盖	版本	A
			X. XX	±0.20	APPROVAL	TITLE	(塑高4.3)	REV.	
			X. XXX	±0.10	比 例	产品料号	PM200-2-N-S-4.3-XX-R(L4.6)	单 位	mm
			Angle	±3.0°	SCALE	PART NO.		页 次	1/1
序号 No.	变更内容 MODIFY CONTENT	日期 MODIFY DATE	投 影		Projection	材 料		SHEET	
						MATERIAL			