



NOTES:

备注

1. Copper, nickel base, matte tin
黄铜H62, 镍底, 镀雾锡
2. Wire screw hole M4
压线螺孔M4
3. Current Rating: 60A
额定电流: 60A
4. Operating temperature: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
工作温度: $-40^{\circ}\text{C} \sim +125^{\circ}\text{C}$
5. There shall be no defects such as pin deformation and burrs.
不得有脚变形, 毛刺等缺陷
6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差



Ordering Information

HC - * * * * - ***** - FD *** * - 02

Type	Screw Thread	Welding Feet	T=Anti Twist (防止扭动)	Series	D=DIP S=SMT FD=Flag Dip	Product No.	Material
M-Pull Teeth (抽牙)	3-M3 (螺牙)	(焊脚)		0808-8x8mm 1620-16x20mm		产品序号	默认-Copper (黄铜)
RN=Rev Nut (铆螺母)	4-M4 (螺牙)	2-2个					BC=Red Copper (紫铜)
RG=Rev Gasket (铆垫片)	5-M5 (螺牙)	4-4个					
	6-M6 (螺牙)	6-6个					
		8-8个					

			GENEER TOLERANCE	制 图 DRAWING	02	 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO.,LTD			
			DIM TOL	审 核 CHECK					
			5 or more ±0.35	批 准 APPROVAL		产品名称 TITLE	PCB 焊接端子 侧插 铆垫片 M4 4焊脚 10x13.5x8mm	版 本 REV.	A
1	初版发行		2~5 ±0.25	比 例 SCALE		产品料号 PART NO.	HC-RG44-1013-FD063-02	单 位 UNITS	mm
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	0~2 ±0.15	投 影 Projection		材 料 MATERIAL		页 次 SHEET	1/1
			Angle ±3.0°						