





Num	Category	Describe
1	Max Current	0.8A
2	Cable gauge (AWG)	14-26 AWG
3	D_SUB connector:	Machine Pin(冲针头)
4	PCB Material	FR4
5	D_SUB Withstanding voltage	300V AC/MINUTE
6	D_SUB Operating temperature	-20℃ to 70℃
7	Rated voltage according to	UL:No
8	Rated current according to	UL:No
9	D_SUB Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L110*W65*H55mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2024. 10. 09				名称	端子台		型号	DB9-G7					
审核							版本	Ver:1.0	客户编号							
核准																
							投影角度		图纸比例		第 1 张 共 1 张					
未注线性公差GB1804-m级 (单位:mm)								1:1	中山市肯博电子科技有限公司 www.kingpow.cn							
尺寸	≤1	3-6	6-30	30-120	120-400	400-1000						1000-2000	2000-4000	角度公差		±0.5°
公差	0.15	0.2	0.3	0.5	0.8	1.2						2.0				