



parameter table:

Num	Category	Describe
1	Max Current	1A
2	Cable gauge (AWG)	16-26 AWG
3	IDC Pitch:	Pitch:2.54mm
4	PCB Material	FR4
5	IDC Withstanding voltage	300V AC/MINUTE
6	IDC Operating temperature	-20℃ to 70℃
7	Rated voltage according to	UL:
8	Rated current according to	UL:
9	IDC Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L110*W65*H55mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2024. 10. 10	名称	端子台	型号	IDC14P-C
审核				版本	Ver:1.0	客户编号	
核准				摄影角度	摄影比例	第 1 张 共 1 张	
未注线性公差GB1804-m级 (单位:mm)				角度公差 ±0.5°		中山市肯博电子科技有限公司 www.kingpow.cn	
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2