






Num	Category	Describe
1	Max Current	0.5A
2	Cable gauge (AWG)	18-26 AWG
3	SCSI Pitch:	Pitch:1.27mm
4	PCB Material	FR4
5	SCSI Withstanding voltage	300V AC/MINUTE
6	SCSI Operating temperature	-20℃ to 70℃
7	Rated voltage according to	UL:
8	Rated current according to	UL:
9	SCSI Material:	INSULATOR:PBT 30%GF; CONTACT:COPPER ALLOY
10	Box size w/label	L110*W65*H55mm
11	Packing	



Pin assignment

制作	Hero. Xu	日期	2024. 10. 10				名称	端子台		型号	SCSI-14P-CN-F	
审核							版本	Ver:1.0	客户编号			
核准												
							摄影角度		图纸比例		第 1 张 共 1 张	
未注线性公差GB1804-m度 (单位:mm)												
尺寸	≤3	3-6	6-30	30-120	120-400	400-1000	1000-2000	2000-4000	角度公差	±0.5°		
公差	0.1	0.15	0.2	0.3	0.5	0.8	1.2	2.0		1:1		
									中山市肯博电子科技有限公司 www.kingpow.cn			