







# NOTES:

备注

- 1.Copper,nickel base,matte tin  
黄铜H62, 镍底, 镀雾锡
- 2.Wire screw hole M4  
压线螺孔M4
- 3.Current Rating: 50A  
额定电流: 50A
- 4.Operating temperature: -40℃ ~ +125℃  
工作温度: -40℃ ~ +125℃
- 5.There shall be no defects such as  
pin deformation and burrs.  
不得有脚变形, 毛刺等缺陷
- 6.Unmarked dimensions refer to tolerances  
未标注的尺寸参考公差



参考安装方式

## Ordering Information

HC - \* \* \* \* - D \* \* \* \* - 02

| Type                     | Screw Thread | Welding Feet | T=Anti Twist | Series       | D=Pin          | Product No. | Material          |
|--------------------------|--------------|--------------|--------------|--------------|----------------|-------------|-------------------|
| M=Pull Teeth<br>(抽牙)     | S=M5 (螺牙)    | 01脚          | (防止扭动)       | 0808-8x8mm   | S=SMT          | 产品序号        | 默认=Copper<br>(黄铜) |
| RS=Rivet Nut<br>(铆螺母)    | 4=M4 (螺牙)    | 2个           | .....        | 1620-16x20mm | FD=Flag<br>Dip |             | 默认=Copper<br>(黄铜) |
| RG=Rivet Gasket<br>(铆垫片) | S=M5 (螺牙)    | 4个           |              |              |                |             |                   |
|                          | 6=M6 (螺牙)    | 6个           |              |              |                |             |                   |
|                          |              | 8个           |              |              |                |             |                   |

|           |                        |                   |                   |                  |    |                                                          |                                          |             |     |
|-----------|------------------------|-------------------|-------------------|------------------|----|----------------------------------------------------------|------------------------------------------|-------------|-----|
|           |                        |                   | GENERAL TOLERANCE | 制图<br>DRAWING    | 02 | 深圳市华灿天禄电子有限公司<br>ShenzhenhuacantianluELECTRONICS CO.,LTD |                                          |             |     |
|           |                        |                   | DIM TOL           | 审核<br>CHECK      |    | 产品名称<br>TITLE                                            | PCB 焊接端子 插板 铆垫片 M4<br>4焊脚 7.9x7.9x24.3mm | 版本<br>REV.  | A   |
|           |                        |                   | 5 or more ±0.35   | 批准<br>APPROVAL   |    | 产品料号<br>PART NO.                                         | HC-RG44-0707-D059-02                     | 单位<br>UNITS | mm  |
| 1         | 初版发行                   |                   | 2~5 ±0.25         | 比例<br>SCALE      |    | 材料<br>MATERIAL                                           |                                          | 页次<br>SHEET | 1/1 |
| 序号<br>No. | 变更内容<br>MODIFY CONTENT | 日期<br>MODIFY DATE | 0~2 ±0.15         | 投影<br>Projection |    |                                                          |                                          |             |     |
|           |                        |                   | Angle ±3.0°       |                  |    |                                                          |                                          |             |     |