








参考安装方式

NOTES:

备注

1. Copper, nickel base, matte tin
黄铜H62, 镍底, 镀雾锡

2. Wire screw hole M4
压线螺孔M4

3. Current Rating: 50A
额定电流: 50A

4. Operating temperature: -40°C ~ +125°C
工作温度: -40°C ~ +125°C

5. There shall be no defects such as
pin deformation and burrs.

不得有脚变形, 毛刺等缺陷

6. Unmarked dimensions refer to tolerances
未标注的尺寸参考公差

Ordering Information

HC - * * * - * * * - D * * * * - 02

Type	Screw Thread	Welding Feet	Series	D-BIP	Product No.	Material
M-Pull Teeth (插牙)	3-M3 (螺牙)	0808-8mm (焊脚)	0808-8mm	S-SMT	产品序号	默认-Copper (黄铜)
BN-Rivet Nut (铆螺母)	4-M4 (螺牙)	2-2个	163D-16x20mm	FD-Flag		BC-Roof Copper (紫铜)
RG-Rivet Gasket (铆垫片)	5-M5 (螺牙)	4-4个		0ip		
	6-M6 (螺牙)	6-6个				
		8-8个				

			GENERAL TOLERANCE	制 图 DRAWING	02					 深圳市华灿天禄电子有限公司 ShenzhenhuacantianluELECTRONICS CO., LTD	
			DIM TOL	审 核 CHECK							
			5 or more ±0.35	批 准 APPROVAL	产品名称 TITLE	PCB 焊接端子 插板 铆垫片 M4 4焊脚 8x8x8.2mm			版 本 REV.	A	
1	初版发行		2~5 ±0.25	比 例 SCALE	产品料号 PART NO.	HC-RG44-0808-D052-02			单 位 UNITS	mm	
序号 No.	变更内容 MODIFY CONTENT	日 期 MODIFY DATE	0~2 ±0.15	投 影 Projection		材 料 MATERIAL				页 次 SHEET	1/1
			Angle ±3.0°								