ROHS

Http://www.krhro.com











SCHEMATIC

Model No.	DC-044S-20A	DC-044S-25A
PIN	ø2.0	ø2.5

Rating: 3A 30V DC
Contact Resistance: 30 mΩ Max.
Operating temperature:-30℃~70℃
Operating force:3-30N
Operating Life:5,000cycles

ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK
②	Terminal	———	3	Brass	Ag Plating	———
①	Housing	———	1	PPA	Black	———

APPROVALS		DATE	
DRAWN	LIUCAN	2021.5.28	
CHECKED			TITLE: PHONE JACKES
APPROVALS			PART NO.

TOLERANCES ARE			ANGLE	UNIT: mm	SCALE: 1:1	PROJ:
	30~以上	±0.30				
	10~30	±0.20				
	5~10	±0.15	±2°	DRAWING NO.	———	SHEET 1 OF 1
	~ 5	±0.10				

ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.
———	A	———	NEW	———	———	———