

Specifications

Ordering Information

F185-11 XX A0 A SY E 2

备注(Remark)

1. 材料(MATERIAL)

胶芯: PBT+30%G.F UL94V-0, 颜色: 黑色.

Housing: PBT+30%G.F UL94V-0, Color: Black

端子: 青铜, 镍底30u", 表面镀普金

Contact: bronze, GOLD PLATING OVER ALL

30u" NICKEL UNDERPLATING OVER ALL

2. 特性 (characteristics):

额定电流: 3 AMP

Rating Current: 3 AMP.

接触阻抗: 20 mΩ MAX.

Contact Resistance: 20 mΩ MAX.

绝缘阻抗: 1000 MΩ MIN.


Insulating Resistance: 1000 MΩ MIN.

耐电压: AC 500V/分钟.

Withstanding Voltage: AC 500V/Minute.


温度范围: -40° C to +105° C

Temperture Range: -40° C to +105° C



Recommended P.C.B LAYOUT

General Tolerance ±0.05



NO. OF PINS
PER ROW
1~40P

Full of Gold
A0=0.8u"
A1=1u"
A2=1.5u"
A3=2u"
A4=3u"
A5=5u"
A6=10u"
A7=15u"
A8=20u"
A9=30u"
S1=Ordinary Tin Plated
S2=Matte Tin Plated
S3=Tin-plated High-temperature

Contact Plating
Semi-gold
B0=0.8u"
B1=1u"
B2=1.5u"
B3=2u"
B4=3u"
B5=5u"
B6=10u"
B7=15u"
B8=20u"
B9=30u"

INSULATOR MATERIAL:
A: PBT
B: PA6T
C: PA9T
D: LCP

PACKING
A: PE Bag
B: Tape & Reel
C: Tube
D: Tube+CAP
E: Tray

REV	DATE	SYMBOL	MODIFICATION DESCRIPTION	OPERATION		SCALE		Fit		DESIGN	PART NO.	TITILE	Customer No.
				X.X	±0.25	UNIT	MM	SI ZE	A4				
				X.XX	±0.20			SHEET	1/1	CHECK			
				X.XXX	±0.10			PROJ.		APPROVE			
				Angle	±3°								
				DIM	TOL								

Yxcon

东莞市宇熙精密连接器有限公司

www.yxcon.com

Dongguan Yuxi Electronic Co., Ltd.

赵文品 2024. 11. 06

F185-11XXA0ASYE2

2.54mm 单排母 塑高8.5 1*XXP 镀普金 PBT
180度 Y型 DIP:3.0 盒装