







REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	05/20/2020	PECK



- Note:
- Material:
 - Housing: High temperature thermoplastic,UL94v-0
 - Orbit: High temperature thermoplastic,UL94v-0
 - Contact: copper alloy;;
Gold plated contact area;Tin plated solder area
 - Shell:Stainless;Ni plated allover;
Gold plated solder area
 - Specification:
 - Current rating: 0.5A Max
 - Voltage rating: 5V DC
 - Dielectric withstanding voltage:
500V(AC) for 1 min.
 - Contact resistance: 100mΩ Max.
 - Insulation resistance: 1000MΩ min.
 - Temperature range: -25°C~85°C

4	FPC 0.5mm间距A型-焊片		PhosphorBronze T=0.20MM	镀锡	2 PCS		A ₂
3	FPC 0.5mm间距A型-锁扣(窄扣)		SEE TABLE	—	1 PCS		A ₂
2	FPC 0.5mm间距A型卧贴上接-PIN		PhosphorBronze T=0.20MM	镀锡	Nx1 PCS		A ₂
1	FPC 0.5mm间距A型卧贴-基座		SEE TABLE	—	1 PCS		A ₂
序号	品 名		材料规格	电镀方式/颜色	使用数量	备 注	版本

DIMENSION CLASSIFICATION ■ : CRITICAL ☒ : MAJOR			台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD							
			TITLE		05DS-XXPS					開關, 連接器 SOFNG
TOLERANCE TABLE										
.X	±	0.40	PART NO.	05DS-XXPS			SERIES	SD106		
.XX	±	0.25	APPROVED	Peck	DWG NO.		SOF-G006			
.XXX	±	0.10	CHECKED	Paul	SCALE	1:1	UNIT	mm	SIZE	A4
ANGLE	±	2°	DRAWIN	David			REV	AO	SHEET NO.	1/1