




PCB Layout(Pattern side)



NO.1			
PART NO	H	PART NO	H
E	6	N	10.5
F	6.5	O	11
G	7	P	11.5
H	7.5	Q	12
I	8	R	12.5
J	8.5	S	13
K	9	T	13.5
L	9.5	U	14
M	10	V	15

NO.2	
PART NO	vigor
4	250±30
5	350±50

NO.3	
PART NO	MATERIAL/QTY
S	SUS/1PC
C	C5210/1PC
D	SUS/2PCS
F	C5210/2PCS

NO.4-NO.5	
PART NO	NOTE
01~99	SERIAL NUMBER

⑦	Gasket	—	1	PPA	—	—
⑥	Waterproof Silicone	—	1	Silica gel	—	—
⑤	Terminal	—	4	Brass(0.3t)	Plating silver	—
④	Contact	—	1	F.Ag/SUS	—	—
③	Base	—	1	PPA	Black	—
②	Cover	—	1	PPA	—	—
①	Keystoke	—	1	PPA	Black	—
ITEM	PART NAME	TER'NO.	QTY.	MATERIAL	FINISHING	REMARK

APPROVALS		DATE		 hro®		
DRAWN	LIUCAN	2022.10.25				
CHECKED				TITLE:	TACT SWITCHS	
APPROVALS				PART NO.	K2-1841DP-□□□W-□□	
TOLERANCES ARE		30~以上	±0.30	ANGLE	UNIT: mm	SCALE: 1:1
		10~30	±0.20			
		5~10	±0.15			
		~ 5	±0.10			
		±2'		DRAWING NO.	_____	PROJ: 
						SHEET 1 OF 1

	A					
ECN NO.	REV.	DATE.	DESCRIPTION.	CHANGE.	CHECK.	APPRO.