






1	VCC	+5V
2	-DATA 0	Neagative Data Channel 0
3	+DATA 0	Positive Data Channel 0
4	GND	Ground

Material declaration		
No.	NAME	Description
① A	胶芯	LCP 30% UL94V-0 耐热塑胶
② B	接触端子	磷铜 C5191 (镀金 1u" / 焊尾雾锡)
③ C	外壳	黄铜 C2680/SPCC [镀镍 50u" min]

DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司		TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD		SOFNG	
		TITLE	USB-102SD-P4 [卧贴式 6.3短体无导线USB连接器]	SERIES	SD106	開關, 連接器	
TOLERANCE TABLE		PART NO.	USB-102SD-P4	APPROVED	Peck	DWG NO.	SOF-G006
.X	± 0.40	CHECKED	Paul	SCALE	1:1	UNIT	mm
.XX	± 0.25	DRAWIN	David	REV	AO	SHEET NO.	1/1
.XXX	± 0.10						
ANGLE	± 2°						