







REVISION			
LTR	DESCRIPTION	DATE	APP
A0	NEW RELEASE	08/23/2021	PECK



原理图



SPECIFICATION:

- 1,CURRENT RATING:DC 12V 0.1A.
- 2,DIELECTRIC WITHSTANDING VOLTAGE:
500V AC R.M.S. FOR ONE MINUTE.
- 3,INSULATION RESISTANCE:100M OHMS MIN.
AT 500V DC
- 4,CONTACT RESISTANCE:80m OHMS MAX.
- 5,OPERATING TEMPERATURE:-20°C TO
+80°C.
- 6,OPERATING LIFE:10,000 CYCLES.

DIMENSION CLASSIFICATION ■ : CRITICAL ☒ : MAJOR		台灣碩方精密電子科技有限公司 TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD							
		TITLE	MS-213J 微型正拨式开关			開關, 連接器 SOFNG			
TOLERANCE TABLE									
.X	± 0.40	PART NO.	SOF-G006				SERIES	SD106	
.XX	± 0.25	APPROVED	Peck	DWG NO.		MS-213J			
.XXX	± 0.10	CHECKED	Paul	SCALE 1:1		UNIT	mm	SIZE	A4
ANGLE	± 2°	DRAWIN	David			REV	AO	SHEET NO.	1/