






General tolerances(mm)													0.1/10 ±2°
0 ~ 3	>3 ~ 6	>6 ~ 10	>10 ~ 18	>18 ~ 30	>30 ~ 50	>50 ~ 80	>80 ~ 120	>120 ~ 180	>180 ~ 250	>250 ~ 315	>315 ~ 400	>400 ~ 500	
±0.12	±0.18	±0.22	±0.26	±0.31	±0.37	±0.57	±0.80	±0.93	±1.05	±1.15	±1.60	±2.20	±2.50



Product model	PIN	A	B	C
BX-DGVC-5.08-2P	2	12.16	5.08	5.08
BX-DGVC-5.08-3P	3	17.24	10.16	10.16
BX-DGVC-5.08-4P	4	22.32	15.24	15.24
BX-DGVC-5.08-5P	5	27.40	20.32	20.32
BX-DGVC-5.08-6P	6	32.48	25.40	25.40
BX-DGVC-5.08-7P	7	37.56	30.48	30.48
.....				
BX-DGVC-5.08-24P	24	5.08xN+2	5.08x(N-1)	5.08x(N-1)

UL Standard	B	C	D
Rated Voltage(V)/Current(A)	300/15	/	300/10
IEC Standard			
Overvoltage Category/Pollution Degree	Ⅲ/3	Ⅲ/2	Ⅱ/2
Rated Voltage(V)/Current(A)	/	320/20	/
Rate Impulse Voltage(KV)	/	4	/
Pitch(mm)/Poles	5.08/N=02~24P		
Operating temperature(°C)	-40°C~+105°C		
Conform to RoHS	Yes		

2	Pin	Copper	Sn Plated
1	Housing	PA66	UL94V-0
ITEM	NAME OF PART	MATERIAL	NOTES

2	端子 Contact	黄铜	n×1	电镀铜: 整个表面镀层30u"MIN, 厚度 80u"MIN.
1	基座 Wafer	PA66(UL94V-0)	1	白色
序号	名称	材料	数量	备注

GENERAL TOLERANCES				DRAWN BY					
0.X ±0.25		X.° ±3°		CHK.BY					
0.XX ±0.12				APRV.BY					
0.XXX ±0.05		X.X° ±0.5°			SHEET	PROD. NAME Socket-type terminal			
UNIT	SIZE	SCALE		DRAWING NO.	1 OF 1	PART NO. BX-DGVC-5.08-NP			
MM	A4	1:1			TITLE				