






1	VCC	+5V
2	-DATA 0	Neegative Data Channel 0
3	+DATA 0	Positive Data Channel 0
4	GND	Ground



PCB LAYOUT



NOTES:

- MATERIAL SPECIFICATION:
 - HOUSING: THERMOPLASTIC (UL94V-0)
 - SHELL: SEE PART NO.
PLATING: NICKEL
 - TERMINAL: COPPER ALLOY
PLATING: GOLD/TIN PLATED;
- ELECTRICAL CHARACTERISTIC:
 - VOLTAGE CURRENT RATING: 1AMP, 30V DC;
 - INSULATION RESISTANCE: 1000M Ω MIN;
 - CONTACT RESISTANCE: 30m Ω MAX;
 - WITHSTANDING VOLTAGE: 500V AC;
- MECHANICAL:
 - MATING FORCE: 3.5 KG MAX
 - UNMATING FORCE: 1.02 KG MIN.

DIMENSION CLASSIFICATION		台灣碩方精密電子科技有限公司				開關, 連接器	
■ : CRITICAL		TAIWAN SOFNG PRECISION ELECTRONIC CO., LTD				SOFNG	
☒ : MAJOR		TITLE				USB-309	
TOLERANCE TABLE		PART NO.				SERIES	
.X	± 0.40	SOF-G006				SD106	
.XX	± 0.25	APPROVED		DWG NO.		USB-309	
.XXX	± 0.10	CHECKED		SCALE 1:1		UNIT mm	
ANGLE	± 2°	DRAWIN		REV		SHEET NO.	
		David		A0		1/1	