

Operation:DIP/卧插式 双层导边短体型 2.0USB 连接器

(Type-A)



ITEM NO.: USB-128 (Series)

(L11.5mm×W14.5mm×H16.0mm)

表面插装 DIP

側向操作 LATERAL

精密部品 NICETY

可靠 STABILIZE

適合環保 RoHS

Technical parameter

PROJECT \ LEVEL		A[better product]	B[average product]
Electrical Properties	Contact Rating	0.25A, 24V DC	
	Initial Contact Resistance	50mΩ max.	
	Insulation Resistance	100MΩ min.500V DC Skey/PD: 100MΩ min.300V DC	
Durable Performance	Withstand Voltage	500V AC for 1 minute	350 V AC for 1 minut
	There No Load	6,000 Cycles	5,000 Cycles
	Rated Load	5,000 Cycles	4,000 Cycles
Storage temp.		-35℃~+75℃(Operating Temp:)	
Operating Force		IF:20N MAX. (EF:10.0N MIN.)	
Heat Rrsistance		IR Reflow:235℃, 5sec. Manual:350℃, 3sec.	


Material declaration

No.	NAME	Description
① A	胶芯	PA66 耐热尼龙
② B	接触端子	磷铜 C5191 (镀金 1u" /焊尾雾锡)
③ C	外壳	黄铜 C2680/SPCC[镀镍 50u" min]

PIN SIGNAL

1/5	VCC	+5V
2/6	-DATA 0	Neagative Data Channel 0
3/7	+DATA 0	Positive Data Channel 0
4/8	GND	Ground

Unit:mm



P.C.B LAYOUT

