

HEADERS & RECEPTACLES



TE CONNECTIVITY (TE)
AMP MONO-SHAPE TAB CONN 7P. LIF UP
10A



RAST | RAST 5 IDC Connectors



293143-1

TE Internal Number: 293143-1

Always EU RoHS/ELV Compliant

Number of Positions **7**

Color **Violet**

✓ Active

 **PRODUCT DRAWING**
English

 **3D PDF**

Product Drawings

AMP MONO-SHAPE L.I.F TAB CONNECTORS 2-10 POS

PDF
English

CAD Files

3D PDF

PDF
3D

Customer View Model

2D_DXF.ZIP
English

Customer View Model

3D_IGS.ZIP
English

Customer View Model

3D_STP.ZIP
English



Please review product documents or [contact us](#) for the latest agency approval information. Please Note: Use the Product Drawing for all design activity.



 **Product Type Features**

Connector Style

Receptacle



Applies To

Printed Circuit Board

Configuration Features

Number of Positions

7

Short Circuit Position

None

Backwall/Post Interruptions

Without

Connector Configuration

LIF

Body Features	Color	Violet
Contact Features	Contact Type	Tab
	Contact Plating Material	Tin
	Contact Layout	Inline
	Contact Base Material	Brass
Mechanical Attachment	Locking Latch Between Cavity Number	None
	Polarizing Rib Location	4D, 6D
Housing Features	Inside Polarization Key Location	None
	Housing Material	PA 6.6 GF
	Housing Color	Gray
Dimensions	Length	34.9 mm [1.37 in]
	Height	9.2 mm [.36 in]
Operation/Application	For Use With	RAST 5 Header
Industry Standards	RAST Version	None
Packaging Features	Packaging Method	Tray, Tray/Box
	Packaging Quantity	455
Product Compliance	Statement of Compliance PDF	
	VIEW ALL PRODUCT COMPLIANCE	