




Pushing Performance  
Since 1945

# Han-Eco 10B-Cover-w. SL-w. cord-HTE/HSE



|               |                                         |
|---------------|-----------------------------------------|
| Part number   | 19 43 010 5442                          |
| Specification | Han-Eco 10B-Cover-w. SL-w. cord-HTE/HSE |

## Identification

|                              |                  |
|------------------------------|------------------|
| Category                     | Accessories      |
| Series of hoods/housings     | Han-Eco® B       |
| Type of accessory            | Protection cover |
| Description of the accessory | for hoods        |

## Version

|              |                      |
|--------------|----------------------|
| Size         | 10 B                 |
| Locking type | Single locking lever |

## Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Number of relockings                   | ≥500            |
| Degree of protection acc. to IEC 60529 | IP66            |

## Material properties

|                                           |                                          |
|-------------------------------------------|------------------------------------------|
| Material (hood/housing)                   | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | RAL 9005 (jet black)                     |
| Material (seal)                           | NBR                                      |
| Colour (seal)                             | RAL 9005 (jet black)                     |
| Material (locking)                        | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (locking)                          | RAL 9005 (jet black)                     |
| Material flammability class acc. to UL 94 | V-0                                      |



**Pushing Performance**  
Since 1945

## Material properties

Material flammability class acc. to UL 94  
(locking levers)

V-0

RoHS

compliant

ELV status

compliant

China RoHS

e

REACH Annex XVII substances

Not contained

REACH ANNEX XIV substances

Not contained

REACH SVHC substances

Not contained

Fire protection on railway vehicles

EN 45545-2 (2020-08)

Requirement set with Hazard Levels

R22 (HL 1-3)  
R23 (HL 1-3)

## Specifications and approvals

Specifications

IEC 61984  
EN 45545-2 Fire protection on railway vehicles

## Commercial data

Packaging size

1

Net weight

60 g

Country of origin

Germany

European customs tariff number

85389099

GTIN

5713140829800

ETIM

EC002314

eCl@ss

27440208 Cap for industrial connectors