



Pushing Performance  
Since 1945

# Han-Eco 24B-Cover w. bearing bracket



Image is for illustration purposes only. Please refer to product description.

|               |                                      |
|---------------|--------------------------------------|
| Part number   | 19 43 024 5410                       |
| Specification | Han-Eco 24B-Cover w. bearing bracket |

## Identification

|                              |                                                               |
|------------------------------|---------------------------------------------------------------|
| Category                     | Accessories                                                   |
| Series of hoods/housings     | Han-Eco® B                                                    |
| Type of accessory            | Protection cover                                              |
| Description of the accessory | for bulkhead mounted housings<br>for surface mounted housings |

## Version

|              |                      |
|--------------|----------------------|
| Size         | 24 B                 |
| Locking type | Single locking lever |

## Technical characteristics

|                                        |                 |
|----------------------------------------|-----------------|
| Limiting temperature                   | -40 ... +125 °C |
| Number of relockings                   | ≥500            |
| Degree of protection acc. to IEC 60529 | IP66            |

## Material properties

|                                           |                                          |
|-------------------------------------------|------------------------------------------|
| Material (hood/housing)                   | Polyamide (PA)<br>Fibre-glass reinforced |
| Colour (hood/housing)                     | RAL 9005 (jet black)                     |
| Material flammability class acc. to UL 94 | V-0                                      |
| RoHS                                      | compliant                                |
| ELV status                                | compliant                                |
| China RoHS                                | e                                        |
| REACH Annex XVII substances               | Not contained                            |



Pushing Performance  
Since 1945

Material properties

|                                     |                      |
|-------------------------------------|----------------------|
| REACH ANNEX XIV substances          | Not contained        |
| REACH SVHC substances               | Not contained        |
| Fire protection on railway vehicles | EN 45545-2 (2020-08) |
| Requirement set with Hazard Levels  | R22 (HL 1-3)         |
|                                     | R23 (HL 1-3)         |

Specifications and approvals

|                |                                                |
|----------------|------------------------------------------------|
| Specifications | IEC 61984                                      |
|                | EN 45545-2 Fire protection on railway vehicles |

Commercial data

|                                |                                        |
|--------------------------------|----------------------------------------|
| Packaging size                 | 1                                      |
| Net weight                     | 35 g                                   |
| Country of origin              | Germany                                |
| European customs tariff number | 85389099                               |
| GTIN                           | 5713140829749                          |
| ETIM                           | EC002314                               |
| eCl@ss                         | 27440208 Cap for industrial connectors |