

A

A

B

B

C

C

由Autodesk教育版产品制作

F



F

G

G

H





H



NOTES
ELECTRICAL
1. VOLTAGE RATING : 125 VAC RMS.
2. CURRENT RATING : 1.5 AMP.
3. CONTACT RESISTANCE : 40 MILLIOHMS MAX.
4. INSULATION RESISTANCE : 500 MEGOHMS MIN @ 100V DC .
5. DIELECTRIC DIELECTRIC RESISTANCE : 500V DC RMS 50Hz. 1MIN.

MECHANICAL
1. DURRABILITY : 750 CYCLES MIN.
2. MATING/UNMATING FORC: 2.24 KG. F MAX.

ENVIRONMENTAL :
1. OPERATION : -40℃~+85℃.
2. STORAGE : -40℃~+85℃.



PCBLAYOUT T=1.6
TOL:±0.05

3408 - 03 0 - XX

系列码
RJ45 立式12.7H
类别码
03:SMT有壳无灯无柱
流水码
13:3u" LCP黑 盘装
23:3u" LCP黑 卷装

5	RJ45 立式12.7H SMT无灯外壳	1	C2680 T=0.2mm	镍40u"
4	RJ45 立式12.7H接地片	1	C2680 T=0.35mm	亮锡100u"
3	RJ45 立式12.7H端子	8	C5191 T=0.35mm	Au/亮锡100u"/NI 50u"
2	RJ45 立式12.7H SMT插芯半成品	1	LCP UL94V-0	BLACK
1	RJ45 立式12.7H无柱有灯主体	1	LCP UL94V-0	BLACK
NO.	PART NAME	Q'TY	MATERIAL	PLATING & COLOR

				OPERATION		SCALE		Fit		Yxcon 东莞市宇熙精密连接器有限公司 www.yxcon.com Dongguan Yuxi Electronic Co.,Ltd.			
				X.X	±0.35	UNIT		MM					
				X.XX	±0.25	SIZE	A4	DESIGN	赵文品2024.11.06	PART NO	RJ45-3408-030-13		
				X.XXX	±0.05	SHEET	1/1	CHECK		TITLE	RJ45 立式12.7H SMT无柱有壳无灯3u" LCP黑		
				Angle	±2°	PROJ.		APPROVE		Customer No.			
REV	DATE	SYMBOL	MODIFICATION DESCRIPTION		DIM	TOL							